

SP5 S

Fixed site sampler in stainless steel housing with thermostatic control for automatic sample extraction according to the vacuum principle. Mains operation 230V/50Hz.

Type	Fixed site sampler
Housing	Double-walled stainless steel (material 1.4301/ SS304) / PS / PC (GF10) with 40 mm insulation. Housing separated in sample compartment and control compartment, each with lockable door. Upper door with plexiglass window. Protective top made of Styrosun which can be opened for connection and maintenance works. Option: material 1.4571/ SS316Ti; SS304 EPOXY-coated; SS316Ti EPOXY-coated
Thermostatic control	Self-contained, controlled cooling / heating with 4 settings, no-frost. independent of the programmable controller, Temperature in sample compartment: 4°C (adjustable from 0,0-9,9°C)
Control	Microprocessor control, Sleep-Mode (<5mA), power supply 8-16 V foil keyboard (with keys 0-9, ESC, ENT, cursor), graphical display (128*64 Pixel), back lit
Data logger	3000 entries, nonvolatile data memory; storage of sampling and malfunction data like sample extractions, bottle changes, messages, external signals. optional with I/O add-on-board expandable to 32GB
Programming	12 freely programmable user programs, with function to link programs.
Program start options	Immediately; at a certain time; by an external signal
Program stop options	End of sampling program after one program run; continuous operation or x-runs
Pause mode	Interruption of program run at any time
Overfilling protection	Adjustable from 1 -999 samples/bottle
Interval setting	1 min. to 99 h 59 min. in steps of 1 minute
Pulse setting	1 to 9999 pulses/sample
Manual sample extraction	Possible at any time without interrupting the current program run
Program protection	Up to 5 years after voltage loss
Interface	Mini-USB, RS422/485, RS 232 optional: Ethernet RJ45
Communication	Optional: Modbus, connection via DP PROFIBUS Optional: LAN/WLAN via TCP/IP RJ45, with IE-Browser, memory 4-32GB SD/SDHC
Languages	Multi-language, selectable
Signal inputs	<ul style="list-style-type: none"> • 2 x analogue: 0/4-20 mA, • 8 x digital (flow, event, 1 inputs can be programmed freely) option: expandable with 4x digital, 3 inputs can be programmed freely, and 8x analogue 0-20 mA or 0-10 V, Impulslength 60ms, switching level 7-24 V, max. working resistance 500 Ohm, max. length of signalcable 30 m
Signal outputs / status messages	<ul style="list-style-type: none"> • 8 digital outputs, 1x of them as collective malfunction message option: expandable with 8 digital, 5 are freely programmable (in total 6 messages)

Sampling method	-Vacuum system 20-350 ml Option: vacuum system 20-500 ml Option: vacuum VAR flow-proportional system 5-250 ml Option: bypass system 20-250 ml Option: peristaltic pump
Single sample volume accuracy	Vacuum system: < 2,5 % or +- 3 ml Peristaltic pump: +- 5 % or +- 5 ml
Suction height	Max. 7,5 m [at 1013hPa and stagnant medium], optional 8,5 m
Pumping speed	>0,5 m/s at suction height up to at least 7,8 m [at 1013h Pa]; pump capacity can be adjusted electronically
Suction hose	PVC, L=7,5 m, ID=12 mm. Max. hose length 30 m
Sampling modes	Time-related, flow-dependent, flow-proportional, event-related, manual sample extraction
Bottle variants	Plastic 1 x 25 L, 1 x 50 L, 2 x 10 L 4 x 6,0 L, 4 x 10 L, 4 x 14 L, 12 x 2,9 L, 24 x 1,0 L Glass 12 x 2,0 L 24 x 1,0 L
Overall dimensions	Standard (h x w x d): 1.290 (1.890*) x 690 x 645 mm As measuring station: 1.470 (2.070*) x 690 x 645 mm *) with opened top
Weight	Approx. 100 kg with composite container, higher weight when using several bottles and/or glass bottles
Power supply	230 V / 115 V / AC
Power requirement	Approx. 350VA (with cooling)
Ambient temperature	-20 – 43°C
Sample temperature	0 – 40°C
Standards	CE, Sampling according to ISO 5667-2/3-10
Wetted materials	PC, PVC, Silicone, PS, PE, EPDM [optional: metering vessel glass Duran50, sinker weight SS304]

Make: MAXX

Type: SP5 S

Manufacturer: MAXX Mess- und Probenahmetechnik GmbH,
Hechinger Straße 41, D-72414 Rangendingen
Phone +49(0)7471-98481 0, Fax +49(0)7471-98481 44
e-mail: info@maxx-gmbh.com
internet: www.maxx-gmbh.com

Subject to technical changes. *) Patent No. DE 19726550A1, DE 19726549A1 and VAR unit DE 10008623.3